



# Tie, Insulator Top

by FARGO  
Catalog ID: GJ625FC



\* Representative image

Composite Top Tie

- Semi-Conductive tie provides uniform electrical field around attachment point.

## Product Details

### General

Color Code	Red
Insulator Throat Neck Type	J Neck
Material	Composite
Material - Cover and Body	Semi-Conductive covering over Rigid Black PVC
Product Category	Ties
UPC	096359356271

### Dimensions

Insulator Throat Diameter - Maximum	4 in
Insulator Throat Diameter - Minimum	3.38 in
Insulator Throat Diameter Range	3.38 - 4
Length	26.000 in
Weight	0.372 lb

### Conductor Related

Conductor Diameter (Covered) - Maximum	1.125 in
Conductor Diameter (Covered) - Minimum	0.92 in
Conductor Diameter (Covered) Range	1.125-0.92
Conductor Type	Covered

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)