

# Tie, Double Arm

by FARGO  
Catalog ID: GJ812FC



Composite Double Pin Tie

- Semi-Conductive tie provides uniform electrical field around attachment point.

\* Representative image

## Product Details

### General

Color Code	Green
Insulator Throat Neck Type	F Neck
Material	Composite
Material - Cover and Body	Semi-Conductive covering over Rigid Black PVC
Product Category	Ties
UPC	096359310907

### Dimensions

Insulator Throat Diameter - Maximum	3.38 in
Insulator Throat Diameter - Minimum	2.75 in
Insulator Throat Diameter Range	2.75 - 3.38
Length	13.250 in
Weight	0.490 lb

### Conductor Related

Conductor Diameter (Covered) - Maximum	0.561 in
Conductor Diameter (Covered) - Minimum	0.407 in
Conductor Diameter (Covered) Range	0.561-0.407
Conductor Type	Covered

### Logistics

Pallet Quantity	600 EA
-----------------	--------

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)