

Tie, Double Arm

by FARGO
Catalog ID: GJ815FC



Composite Double Pin Tie

- Semi-Conductive tie provides uniform electrical field around attachment point.

* Representative image

Product Details

General

Color Code	Red
Insulator Throat Neck Type	F Neck
Material	Composite
Material - Cover and Body	Semi-Conductive covering over Rigid Black PVC
Product Category	Ties
UPC	096359310952

Dimensions

Insulator Throat Diameter - Maximum	3.38 in
Insulator Throat Diameter - Minimum	2.75 in
Insulator Throat Diameter Range	2.75 - 3.38
Length	13.250 in
Weight	0.421 lb

Conductor Related

Conductor Diameter (Covered) - Maximum	1.125 in
Conductor Diameter (Covered) - Minimum	0.92 in
Conductor Diameter (Covered) Range	1.125-0.92
Conductor Type	Covered

Logistics

Pallet Quantity	600 EA
-----------------	--------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com