




# Automatic Splice Copper

by FARGO  
Catalog ID: GL111M

Automatic Splice, for #8 SOL, #6 SOL, 10 MM2 Copper, Dia. Range 0.14 - 0.17 in.

- Range taking automatic splice
- For use with copper and Copperweld conductor
- Individually bagged to seal out dirt before use



\* Representative image

## Product Details

### General

Color Code	None
Material	Copper
Material - Gripping Unit	Bronze Alloy
UPC	096359311249

### Conductor Related

Conductor Diameter - Maximum	0.17 in
Conductor Diameter - Minimum	0.14 in
Conductor Diameter Range	0.14 - 0.17
Conductor Type	Copper, Copperweld

### Certifications and Compliance

UL Listed	No
-----------	----

### For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)