




Automatic Splice Copper

by FARGO
Catalog ID: GL112M

Automatic Splice, for 16 MM2 SOL Copper, Dia. Range 0.17 - 0.20 in.

- Range taking automatic splice
- For use with copper and Copperweld conductor
- Individually bagged to seal out dirt before use



* Representative image

Product Details

General

Color Code	None
Material	Copper
Material - Gripping Unit	Bronze Alloy
UPC	096359311287

Conductor Related

Conductor Diameter - Maximum	0.20 in
Conductor Diameter - Minimum	0.17 in
Conductor Diameter Range	0.17 - 0.20
Conductor Type	Copper, Copperweld

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	14000 EA
-----------------	----------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com