



Automatic Splice Bi-Metal (Copper to Aluminum)

by FARGO
Catalog ID: GL117018A

Automatic Splice, Bimetallic, 1/0 AAC , 2/0 AAAC to 2/0 Sol, 1/0 Str CU

- Individually bagged to seal out dirt before use.



* Representative image

Product Details

General

Color Code	None
Material	Aluminum; Copper
Tension Range	0 lb
UPC	096359311423

Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Insulator / Conductor Hole Spacing	0 in
Weight	0.353 lb

Conductor Related

Conductor Compatibility	AAC-Aster-2/0-7;AAAC 6201 Alloy-Azusa-123.3-6/18
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	4800 EA
-----------------	---------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com