




Automatic Splice Copper

by FARGO
Catalog ID: GL118M

Automatic Splice, for 2/0 SOL, 3/0 SOL, 1/0 str, 2/0 str, 70 MM2 Copper,
Dia. Range 0.37 - 0.43 in.

- Range taking automatic splice
- For use with copper and Copperweld conductor
- Individually bagged to seal out dirt before use



* Representative image

Product Details

General

Color Code	None
Material	Copper
Material - Gripping Unit	Bronze Alloy
UPC	096359311485

Conductor Related

Conductor Diameter - Maximum	0.43 in
Conductor Diameter - Minimum	0.37 in
Conductor Diameter Range	0.37 - 0.43
Conductor Type	Copper, Copperweld

Certifications and Compliance

UL Listed	No
-----------	----

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com