




Automatic Splice Copper

by FARGO
Catalog ID: GL130

Automatic Splice, for 500 (19 or 37 str) Copper, Dia. Range 0.80 - 0.81 in.

- Individually bagged to seal out dirt before use.



* Representative image

Product Details

General

| | |
|--------------------------|--------------|
| Color Code | None |
| Material | Copper |
| Material - Gripping Unit | Bronze Alloy |
| UPC | 096359311614 |

Conductor Related

| | |
|------------------------------|--------------------|
| Conductor Diameter - Maximum | 0.81 in |
| Conductor Diameter - Minimum | 0.80 in |
| Conductor Diameter Range | 0.80 - 0.81 |
| Conductor Type | Copper, Copperweld |

Certifications and Compliance

| | |
|-----------|----|
| UL Listed | No |
|-----------|----|

Logistics

| | |
|-----------------|--------|
| Pallet Quantity | 900 EA |
|-----------------|--------|

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com