



# Automatic Splice, Aluminum, Full Tension

by FARGO  
Catalog ID: GL1351A

Automatic Splice, 10,000 Lb, for 652.8 AAC, 556.6 26/7 ACSR, Dia. Range .927 - .940 in.

- ANSI C119.4
- Class A connector
- Maximum design rating 10,000 lb/44.5 kN
- Color coded funnel guides for easy installation



\* Representative image

## Product Details

### General

Color Code	Natural
Material	Aluminum
Trade Name	Fargo
UPC	096359311645

### Dimensions

Weight	1.960 lb
--------	----------

### Conductor Related

Conductor Compatibility	ACSR-Dove-556.5-26/7
Conductor Diameter - Maximum	0.927 in
Conductor Diameter - Minimum	0.927 in
Conductor Diameter Range	0.927 - 0.927
Conductor Type	AAC, AAAC, ACSR

### Certifications and Compliance

UL Listed	No
-----------	----

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscscs@hubbell.com](mailto:hpscscs@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)