



Automatic Splice, Aluminum, Full Tension

by FARGO
Catalog ID: GL1441A



* Representative image

Automatic Splice, 10,000 Lb, for 954 AAC, Dia. Range 1.100 - 1.140 in.

- ANSI C119.4
- Class A connector
- Maximum design rating 10,000 lb/44.5 kN
- Color coded funnel guides for easy installation

Product Details

General

Color Code	Natural
Material	Aluminum
Trade Name	Fargo
UPC	096359311683

Dimensions

Weight	1.764 lb
--------	----------

Conductor Related

Conductor Compatibility	ACSR-Drake-795-26/7;ACSR-Mallard-795-30/19;ACSR-Ruddy-900-45/7;AAC-Magnolia-954-37;AAC-Goldenrod-954-61
Conductor Diameter - Maximum	1.14 in
Conductor Diameter - Minimum	1.1 in
Conductor Diameter Range	1.1 - 1.14
Conductor Type	AAC, AAAC, ACSR

Certifications and Compliance

UL Listed	No
-----------	----

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com