



Automatic Splice Aluminum Full Tension

by FARGO
Catalog ID: GL404AKR

Automatic Splice, Corrosion Resistant, Full Tension, for #2
ACSR/AAAC/AAC. Dia Range .280 - .320 in.

- ANSI C119.4 Class A Connector
- Corrosion Resistant
- Full tension (95% of conductor rated breaking strength unless otherwise noted)
- Color coded funnel guides for easy identification



* Representative image

Product Details

General

Color Code	Red
Material	Aluminum
UPC	096359505594

Conductor Related

Conductor Diameter - Maximum	0.32 in
Conductor Diameter - Minimum	0.28 in
Conductor Diameter Range	0.28 - 0.32
Conductor Type	AAC, AAAC, ACSR

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	3200 EA
-----------------	---------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com