



# Automatic Splice Bi-Metal (Copper to Aluminum)

by FARGO  
Catalog ID: GL40615

Automatic Splice, Bimetallic, 3/0 Stranded AAC, AAAC, ACSR to 2 Stranded Copper

- Individually bagged to seal out dirt before use.



\* Representative image

## Product Details

### General

|               |                  |
|---------------|------------------|
| Color Code    | None             |
| Material      | Aluminum; Copper |
| Tension Range | 0 lb             |
| UPC           | 096359311997     |

### Dimensions

|                                    |          |
|------------------------------------|----------|
| Adjustment Step                    | 0 in     |
| Assembly Rating (Ultimate)         | 0 lb     |
| Insulator / Conductor Hole Spacing | 0 in     |
| Weight                             | 0.784 lb |

### Conductor Related

|                              |   |
|------------------------------|---|
| Conductor Compatibility      | ACSR-Raven-1/0-6/1;AAC-Poppy-1/0-7;AAAC 6201 Alloy-Azusa-123.3-6/18 |
| Messenger Diameter - Maximum | 0 in  |
| Messenger Diameter - Minimum | 0 in  |

### Certifications and Compliance

|           |    |
|-----------|----|
| UL Listed | No |
|-----------|----|

### Logistics

|                 |         |
|-----------------|---------|
| Pallet Quantity | 2800 EA |
|-----------------|---------|

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)