



# Automatic Splice Bi-Metal (Copper to Aluminum)

by FARGO  
Catalog ID: GL41118

Automatic Splice, Bimetallic, 2/0 Stranded AAC, AAAC, ACSR to 3/0 Stranded Copper

- Individually bagged to seal out dirt before use.



\* Representative image

## Product Details

### General

Color Code	None
Material	Aluminum; Copper
Tension Range	0 lb
UPC	096359482994

### Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Insulator / Conductor Hole Spacing	0 in
Weight	1.568 lb

### Conductor Related

Conductor Compatibility	ACSR-Merlin-336.4-18/1
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

### Certifications and Compliance

UL Listed	No
-----------	----

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscscs@hubbell.com](mailto:hpscscs@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)