



# Automatic Splice Bi-Metal (Copper to Aluminum)

by FARGO  
Catalog ID: GL41223

Automatic Splice, Bimetallic, 397.5 (465.4 AAAC, 477 AAC) Stranded ACSR to 300 Stranded Copper

- Individually bagged to seal out dirt before use.



\* Representative image

## Product Details

### General

Color Code	None
Material	Aluminum; Copper
Tension Range	0 lb
UPC	096359312123

### Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Insulator / Conductor Hole Spacing	0 in
Weight	2.156 lb

### Conductor Related

Conductor Compatibility	ACSR-Chickadee-397.5-18/1
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

### Certifications and Compliance

UL Listed	No
-----------	----

### Logistics

Pallet Quantity	400 EA
-----------------	--------

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)