



* Representative image

GP12250S

by Acme Electric
Catalog ID: GP12250S

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 277/480 - 208/277V, 0.25kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	277/480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208/277 V
UL Insulation Class	155°C
UPC	004750310310
Winding Material	CU
kVA	0.3

Dimensions

Height	8.68 in
Length	3.88 in
Weight	12 lb
Width	4.08 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	277/480 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506