



\* Representative image

## GP125000S

by Acme Electric  
Catalog ID: GP125000S

Prop65\_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 277/480 - 208/277V, 5kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## Product Details

### General

Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	277/480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208/277 V
UL Insulation Class	180°C
UPC	047503001097
Winding Material	CU
kVA	5

### Dimensions

Height	14.38 in
Length	7.13 in
Weight	80 lb
Width	10.31 in

### Electrical Ratings

Frequency Rating	60 Hz
------------------	-------

Primary Voltage	277/480 V
-----------------	-----------

#### Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506