



* Representative image

GP12500S

by Acme Electric
Catalog ID: GP12500S

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 277/480 - 208/277V, 0.5kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

| | |
|----------------------|-----------------------------------|
| Construction | Encapsulated |
| Electrostatic Shield | Shielded |
| Max Temperature Rise | 115 Degrees Celsius |
| Mounting Type | Wall |
| Primary Voltage | 277/480 |
| Product Category | Dry Type Distribution Transformer |
| Secondary Voltage | 208/277 V |
| UL Insulation Class | 155°C |
| UPC | 047503001103 |
| Winding Material | CU |
| kVA | 0.5 |

Dimensions

| | |
|--------|---------|
| Height | 9.06 in |
| Length | 4.2 in |
| Weight | 19 lb |
| Width | 4.37 in |

Electrical Ratings

| | |
|------------------|-----------|
| Frequency Rating | 60 Hz |
| Primary Voltage | 277/480 V |

Certifications and Compliance

| | |
|--------------|--------------|
| CSA Standard | C22.2 No. 47 |
| Nema Rating | NEMA 3R |
| UL Standard | UL 506 |