



12" 16K Guy Strain, Clevis / Thimble

by CHANCE Utility
Catalog ID: GS16012CT

12" Fiberglass Guy Strain- 16,000 lb Series- Clevis / Thimble



Product Details

General

| | |
|----------------------------|------------------|
| Description - End Fitting | Clevis - Thimble |
| Strength Rating - Ultimate | 16000 lb |
| Tensile Strength | 16000 lb |
| UPC | 096359036852 |

Dimensions

| | |
|---|----------|
| Diameter - Rod / Tube | 0.625 in |
| Length | 12.00 in |
| Length - Clevis Pin Center to Clevis Bottom | 1.38 in |
| Mounting Bolt Spacing | 20.00 in |
| Weight | 2.8 lb |

Logistics

| | |
|------------------|--------|
| Carton Quantity | 10 EA |
| Pallet Quantity | 720 EA |
| Standard Package | 1 |

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com