



Pole, Strain

by CHANCE Utility
Catalog ID: H1949113

POLE, STRAIN, Strain Poles for conductor yoke plates accommodate a wide range of yoke plate designs and hole spacings. The Strain Poles with a 2" diameter Epoxiglas®- construction, offer 12,000- pounds maximum load capacity with a 1" wide clevis for aluminum conductor yoke plates. Commonly used in deadend rigging, for "V" strings and restrained angles, poles offer two clevis lengths and overall lengths.



Product Details

General

Style	For Bundle Conductor Yoke Plates
UPC	096359039525

Dimensions

Weight	16.66 lb
--------	----------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com