




Epoxiglas Heavy Duty Swivel Hook Ladder W/8" Hooks, 8'

by CHANCE Utility
Catalog ID: H49058

LADDER, 2.5X8' W/8" HOOKS, Epoxiglas Hook Ladders have many applications in high voltage maintenance to position linemen in the most advantageous working location, making line repairs possible at otherwise almost unaccessible places. All hooks are formed from 1"-diameter tempered steel and can be swiveled to best fit various angles on the structure. Steel chains clip to the hooks to assist in securing the ladder to a support. Rung material for both rated ladders are 1.25" Epoxiglas, sand coated.



* Representative image

Product Details

General

Strength Rating - Ultimate	1250 lb
Style	Swivel Hook Ladder
UPC	096359041290

Dimensions

Diameter	2.5 in
Diameter - Hook	8 in
Length	96 in
Side Rail Space	15 in
Weight	48 lb

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com