



\* Representative image

# Ground Clamp - Duckbill - Mounted 6' II-B- 4

by CHANCE Utility  
Catalog ID: HG37061

Duckbill.

## Product Details

### General

Bolt Installation Torque (Recommended)	20 ft-lbs
Handle Type	Hotstick
Jaw Type	Smooth Jaws
Material	Aluminum
Terminal Connection Type	Pressure
UPC	096359038757

### Dimensions

Jaw Opening Size - Maximum	1.162 in
Jaw Opening Size - Minimum	.162 in
Length	6 in
Weight	7.84 lb

### Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Plain Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Plain Terminal

### Certifications and Compliance

Fault Current - ASTM Grade	ASTM Grade 5
----------------------------	--------------

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)