




# 375

Domed Head Plastic Stopping Plug



## Technical Data

Ingress Protection	IP66, IP67
Operating Temperature	-60°C to +75°C
Construction Materials	Manufactured in Polyamide with Nitrile O-Ring
Threadform	M16 to M75 Thread Length 15mm as standard Thread Pitch 1.5mm as standard

### Approvals

Applications	Suitable for Use in Zone 1, Zone 21, Zone 2, Zone 22
Protection Class	Ex II 2GD Ex eb IIC Gb; Ex tb IIIC Db
Construction & Test Standards	IEC/EN 60079-0, IEC/EN 60079-7 and IEC/EN 60079-31
ATEX Certificate No	Baseefa 12ATEX0095X
UKEx Certificate No	UKEx: BAS21UKEX0053X
IECEx Certificate Number	IECEx BAS 12.0065X
Marine Approvals	ABS: 17-LD1653734-PDA Bureau Veritas: 43523/B0
Additional Certifications	EAC: No EA3C RU C-GB.HA91.B.00265/21* EQM: 20-11-27224/Q20-11-000979/NB0007 Inmetro: IEx 15.0291X PESO: P409088 SONCAP: LCOGB049552-0500

### NEC/CEC\*

\*Only marked on request

NEC Protection Class	Class 1 Zone 1 AEx eb IIC Gb Zone 21 AEx tb IIIC Db
CEC Protection Class	Ex eb IIC Gb; Ex tb IIIC Db
c CSA us Certificate	2700364
Construction & Test Standards	CSA C22.2 No 0-10; CSA/UL 60079-0; CSA/UL 60079-7; CSA/UL 60079-31; IEC 60529

## Size Selection

Thread Size	Head Diameter (mm)	Allen Key Socket Size (mm)
M16	23	8
M20	27.5	10
M25	32	10
M32	39	10
M40	49	10
M50	59	10
M63	72	10
M75	84	10

## Ordering Information

Product	Thread Size
375	M32

Part code Example - 375M32