



385

Plastic M20 Breather Drain
 Increased Safety, Dust Protection
 Certified ATEX / IECEx / c CSA us



International Approvals
 CE
 Ex
 IECEx
 INMETRO
 C US

The Hawke plastic breather drain is a cost effective accessory to prevent condensation and drain moisture from hazardous area enclosures. Certified for increased safety and dust protection and dual certified for ATEX/IECEx and NEC/CEC. Supplied with nitrile o-ring and plastic locknut as standard.

Technical Data

Ingress Protection	IP66
Operating Temperature	-60°C to +80°C
Construction Materials	Manufactured in Polyamide with Nitrile O-Ring
Threadform	M20 x 1.5 pitch Thread Length 15mm

Approvals

Applications	Suitable for Use in Zone 1, Zone 21, Zone 2, Zone 22
Protection Class	Ex II 2GD Ex eb IIC Gb; Ex tb IIIC Db
Construction & Test Standards	IEC/EN 60079-0, IEC/EN 60079-7 and IEC/EN 60079-31
ATEX Certificate No	Baseefa 11ATEX0153X
UKEx Certificate No	BAS21UKEX0043X
IECEx Certificate Number	BAS11.0075X
Additional Certifications	EQM: 20-11-27224/Q20-11-000979/NB0007 Inmetro: IEx 15.0208X

NEC/CEC

NEC/CEC Protection Class	Class I, Zone 1, AEx e/Ex eb IIC Gb; Zone 21, AEx/Ex tb IIIC Db
c CSA us Certificate Number	2700364
Construction & Test Standards	CSA C22.2 NO. 0 - 10, CSA/ANSI 60079-0, CSA/ANSI 60079-1, CSA/ANSI 60079-7 and CSA/ANSI 60079-31

Ordering Information

Format for ordering is as follows:

Product	Thread Size
385	M20

Part code example - 385M20