

260 Series

Benchtop DC Insulation Tester

■ The 260 DC Insulation tester performs DC dielectric withstand (hipot) tests. These bench top instruments are designed to test electrical system apparatus and components in an efficient and reliable manner.



FEATURES

- Rack mountable
- Interlock provision
- Adjustable over current protection
- Overload light
- Zero start interlock
- Output shorting relay
- Triple range voltage meter
- Triple range current meter

BENEFITS

Safe and easy benchtop operation

NIST traceable calibration

Accurate measurements independent of load and line variations

Automatic discharge of test object

APPLICATIONS

- Wire and cable
- Capacitors
- Coils and inductors
- High Voltage Tubes

TECHNICAL SPECIFICATION

Model Number	260-*	
System Output (V)	0-60 kV	
Voltage Meter	0-12/30/60kV	
Current Meter	0-0.1/1/10mA	
Overload	1-11mA	
Dimensions (W x H x D)	21 x 15 x 19.5 in (53 x 38 x 79 cm)	
Weight	Net	90 lbs (41kg)
	Shipping	105 lbs (47.6 kg)
Input Voltage & Frequency	* In the model number, designate 'A' for 115V/60Hz input or 'B' for 220V/50Hz input	
Included Items	QTY 1: High Voltage RG8/U, alligator clip, 25ft (7.6m)	
	QTY 1: Grounding stud with screw connection on chassis of controller	
	User's Manual	
	Calibration Certificate	

OPTIONAL EQUIPMENT & ACCESSORIES

Part Number	Description
HHDA13-280	Grounding Stick, 120kV Max Voltage
SPK1-260	Spare Parts Kit for 260
EXT-WARRANTY	One year extended warranty



HHDA13-280 Grounding Stick (pictured above)

OFFICES:

Europe

Haefely Test AG
Birsstrasse 300
4052 Basel
Switzerland

☎ + 41 61 373 4111
☎ + 41 61 373 4912
✉ sales@haefely.com

China

Haefely Test AG Representative Beijing Office
8-1-602, Fortune Street
No. 67, Chaoyang Road, Chaoyang District
Beijing, China 100025

☎ +86 10 8578 8099
☎ +86 10 8578 9908
✉ sales@haefely.com.cn

North America

Hipotronics, Inc.
1650 Route 22 N
Brewster, NY 10509
United States

☎ +1 845 279 3644
☎ +1 845 279 2467
✉ sales@hipotronics.com