


Compression Stirrup

by ANDERSON
Catalog ID: HLS302P

Aluminum Overhead Compression Stirrup

- Protects primary lines from arcing damage. Wide stance gives good stability for installing hotline clamp.



* Representative image

Product Details

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Compression Tool Type	EEI-13A, 1-1/8
Material - Bail	Copper
Material - Body	Aluminum Alloy
Material - Stirrup	Copper
Plating	No
Type	Stirrups
UPC	096359316442

Dimensions

Copper Loop Size	0.258 in
Diameter - Stirrup Nominal Wire	#2 Solid
Height	3.250 in
Weight	0.588 lb
Width - Main Contact	4 in

Conductor Related

Conductor Diameter - Maximum	0.517 in
Conductor Diameter - Minimum	0.414 in
Conductor Diameter Range	0.414 - 0.517
Conductor Type	Aluminum

Logistics

Packaging Type	Bag
Pallet Quantity	1200 EA

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com