


# Compression Stirrup

by ANDERSON  
Catalog ID: HLS35020P

Aluminum Overhead Compression Stirrup

- Protects primary lines from arcing damage. Wide stance gives good stability for installing hotline clamp.



\* Representative image

## Product Details

### General

Bolt Installation Torque (Recommended)	0 ft-lbs
Compression Tool Type	EEL-13A, 1-1/8
Material - Bail	Copper
Material - Body	Aluminum Alloy
Material - Stirrup	Copper
Plating	No
Type	Stirrups
UPC	096359316459

### Dimensions

Copper Loop Size	0.365 in
Diameter - Stirrup Nominal Wire	2/0 Solid
Height	3.250 in
Weight	0.784 lb
Width - Main Contact	4 in

### Conductor Related

Conductor Diameter - Maximum	0.721 in
Conductor Diameter - Minimum	0.607 in
Conductor Diameter Range	0.607 - 0.721
Conductor Type	Aluminum

### Logistics

Packaging Type	Bag
----------------	-----

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)