


Compression Stirrup

by ANDERSON
Catalog ID: HLS50010P

Aluminum Overhead Compression Stirrup

- Protects primary lines from arcing damage. Wide stance gives good stability for installing hotline clamp.



* Representative image

Product Details

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Compression Tool Type	1-5/16
Material - Bail	Copper
Material - Body	Aluminum Alloy
Material - Stirrup	Copper
Plating	No
Type	Stirrups
UPC	096359316473

Dimensions

Copper Loop Size	0.325 in
Diameter - Stirrup Nominal Wire	1/0 Solid
Height	3.750 in
Weight	0.784 lb
Width - Main Contact	4 in

Conductor Related

Conductor Diameter - Maximum	0.814 in
Conductor Diameter - Minimum	0.72 in
Conductor Diameter Range	0.72 - 0.814
Conductor Type	Aluminum

Logistics

Packaging Type	Bag
----------------	-----

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com