



HS2210

by Wiegmann
 Catalog ID: HS2210

N1 Hinged Wireway 2X2X120 Carbon Steel - Gray

- Bodies and covers are fabricated from 16 gauge steel. HS Series combination hinge/screw cover design offers easy access to open top for "lay-in" of wireway. Screws do not need to be removed to open top. Straight sections with knockouts are provided on side walls on wireways.

Product Details

General

| | |
|----------------|---|
| Application | Designed to protect electrical wiring in applications where dirt, dust, oil, and water are not serious problems. All sections are open on one side so wires and cable can be laid in along an entire wireway run. |
| Color | Gray |
| Cover Type | Hinged Cover |
| Enclosure Type | Nema 1 Type Enclosure |
| Finish Type | Polyester Powder |
| Knockouts | Yes |
| Listings | UL, CSA |
| Material | Carbon Steel |
| Type | Wireway |
| UPC | 786725609109 |

Dimensions

| | |
|---------------|----------|
| Actual Height | 2.500 in |
| Actual Width | 2.500 in |
| Depth | 120 in |
| Height | 3 in |
| Weight | 27 lb |
| Width | 3 in |

Certifications and Compliance

| | |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none">• UL• CSA |
| Nema Rating | 1 |
| UL Listed | Yes |