



## HS224

by Wiegmann  
 Catalog ID: HS224

N1 Hinged Wireway 2X2X48 Carbon Steel - Gray

- Bodies and covers are fabricated from 16 gauge steel. HS Series combination hinge/screw cover design offers easy access to open top for "lay-in" of wireway. Screws do not need to be removed to open top. Straight sections with knockouts are provided on side walls on wireways.

### Product Details

#### General

Application	Designed to protect electrical wiring in applications where dirt, dust, oil, and water are not serious problems. All sections are open on one side so wires and cable can be laid in along an entire wireway run.
Color	Gray
Cover Type	Hinged Cover
Enclosure Type	Nema 1 Type Enclosure
Finish Type	Polyester Powder
Knockouts	Yes
Listings	UL, CSA
Material	Carbon Steel
Type	Wireway
UPC	786725608805

#### Dimensions

Actual Height	2.500 in
Actual Width	2.500 in
Depth	48 in
Height	3 in
Weight	9 lb
Width	3 in

#### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	1
UL Listed	Yes