

HS21007

Wall Bracket
Incandescent



HS21007-09 Brushed Nickel
HS21007-15 Chrome
HS21007-125 Bronze

Dimension: 4-5/8" w (A), 9-7/16" ht. (B). Extends 7 1/2" (C)

Description: 1-Lt. Wall Bracket. Mount in "up" or "down" position.

Backplate: Oval Shape: 9-3/8" tall x 4-5/8" wide.

Glass: Etched glass shade: 5-1/2" dia. x 4-7/8" tall. (HS99003-01)

Application: Indoor

Approvals: UL/CUL Damp location listed.

Installation: Fits standard Outlet Box

Lamps: 1 Medium Base lamp, at 60 watts max. (Not Included)

Electrical: 120V, 60 Hz

