

## HS27007

Wall Bracket

Compact Fluorescent



HS27007-09      Brushed Nickel  
HS27007-125    Bronze

**Dimension:** 4 5/8" w (A), 9 1/2" ht. (B). Extends 7 1/2" (C)

**Description:** 1-Lt. Wall Bracket. Mount in "up" or "down" position.

**Backplate:** Oval Shape: 9-3/8" tall x 4-5/8" wide.

**Glass:** Etched glass shade: 5-1/2" dia. x 4-7/8" tall. (HS99003-01)

**Application:** Indoor

**Approvals:** UL/CUL Damp location listed.

**Installation:** Fits standard Outlet Box

**Lamps:** 1 GU24 Base lamp, at 13 watts max. Lamp included. (2700°K)

**Electrical:** 120V, 60 Hz

