

HS27009

Wall Bracket

Compact Fluorescent



HS27009-09 Brushed Nickel
HS27009-125 Bronze

Dimension: 24"w (A), 8"ht. (B). Extends 7 1/2" (C)

Description: 3-Lt. Wall Bracket. Mount in "up" or "down" position.

Backplate: Oval Shape: 24" wide x 4-5/8" tall.

Glass: Etched glass shade: 5-1/2" dia. x 4-7/8" tall. (HS99003-01)

Application: Indoor

Approvals: UL/CUL Damp location listed.

Installation: Fits standard Outlet Box

Lamps: 3 GU24 Base lamps, at 13 watts max. Lamps included. (2700°K)

Electrical: 120V, 60 Hz

