

## HS41001

Pendant  
Incandescent



HS41001-09 Brushed Nickel  
HS41001-125 Bronze

**Dimension:** 16-1/2" w (A), 12" ht. (B). Overall ht. 85-1/4" (C)

**Description:** 1-Lt. Pendant.

**Glass:** Clear Ribbed Glass: 14-7/8" dia. x 7-1/2" tall.

**Application:** Indoor

**Approvals:** UL/CUL Dry Location listed.

**Installation:** Fits standard Outlet Box

**Lamps:** 1 Medium Base lamp, at 100 watts max. (Not Included)

**Electrical:** 120V, 60 Hz, 10' wire

