

HS41005

Chandelier
Incandescent



HS41005-09 Brushed Nickel
HS41005-125 Bronze

Dimension: 24 1/4" w (A), 19" ht. (B). Overall ht. 94" (C)

Description: 5-lt. Chandelier.

Glass: Etched Glass Shade: 7-1/2" dia. x 5" tall. (HS99000-01)

Application: Indoor

Approvals: UL/CUL Dry Location listed.

Installation: Fits standard Outlet Box

Lamps: 5 Medium Base lamps, at 100 watts max. (Not Included)

Electrical: 120V, 60 Hz, 10' wire

