

## HS41008

Mini-Pendant  
Incandescent



HS41008-09    Brushed Nickel  
HS41008-125    Bronze

**Dimension:** 7-1/2" w (A), 7-1/8" ht. (B).  
Stems: (2) 12" ht., (2) 15" ht.

**Description:** 1-Lt. Mini-Pendant. Swivel/hang straight for sloped ceilings.

**Glass:** Etched Glass Shade: 7-1/2" dia. x 5" tall. (HS99000-01)

**Application:** Indoor

**Approvals:** UL/CUL Dry Location listed.

**Installation:** Fits standard Outlet Box

**Lamps:** 1 Medium Base lamp, at 100 watts max. (Not Included)

**Electrical:** 120V, 60 Hz, 10' wire

