

## HS47003

Chandelier  
Compact Fluorescent



HS47003-09 Brushed Nickel  
HS47003-125 Bronze

**Dimension:** 22-3/16" w (A), 17-7/16" ht. (B). Overall ht. 93"(C)

**Description:** 3-Lt. Chandelier.

**Glass:** Etched Glass Shade: 7-1/2" dia. x 5" tall. (HS99000-01)

**Application:** Indoor

**Approvals:** UL/CUL Dry Location listed.

**Installation:** Fits standard Outlet Box

**Lamps:** 3 GU24 Base lamps, at 13 watts max. Lamps included.(2700°K)

**Electrical:** 120V, 60 Hz, 10' wire

