

HS47008

Mini-Pendant
Compact Fluorescent



HS47008-09 Brushed Nickel
HS47008-125 Bronze

Dimension: 7-1/2" w (A), 7-1/8" ht. (B).
Stems: (2) 12" ht., (2) 15" ht.

Description: 1-lt. Mini-Pendant. Swivel / hang straight for installation on sloped ceilings.

Glass: Etched Glass Shade: 7-1/2" dia. x 5" tall. (HS99000-01)

Application: Indoor

Approvals: UL/CUL Dry Location listed.

Installation: Fits standard Outlet Box

Lamps: 1 GU24 Base lamp, at 13 watts max. Lamp included.(2700°K)

Electrical: 120V, 60 Hz, 10' wire

