

HS71014

Flushmount die-cast
Incandescent



HS71014-31 Black

Dimension: 10-3/4" w (A), 6" ht. (B).

Description: 2-Lt. Flushmount die-cast.

Glass: Clear Glass Curved Panels.

Material: Aluminum

Application: Outdoor

Approvals: cCSAus Damp location listed.

Installation: Fits standard Outlet Box

Lamps: 2 Chandelabra Base lamps, at 60 watts each max. (Not Included)

Electrical: 120V, 60 Hz

