

HS71020

Hanging-Die Cast
Incandescent



HS71020-31 Black
HS71020-125 Bronze

Dimension: 7-1/4" w (A), 15-5/8" ht. (B). Overall ht. 53" (C)

Description: 1-Lt. Hanging-Die Cast.

Glass: Clear Flat Glass Panels

Material: Aluminum

Application: Outdoor

Approvals: UL/CUL Damp location listed.

Installation: Fits standard Outlet Box

Lamps: 1 Medium Base lamp, at 100 watts max. (Not Included)

Electrical: 120V, 60 Hz, 6' wire

