

HS77020

Hanging-Die Cast
Incandescent



HS77020-31 Black
HS77020-125 Bronze

Dimension: 7-1/4" w (A), 15-5/8" ht. (B). Overall ht. 53" (C)

Description: 1-Lt. Hanging-Die Cast.

Glass: Frosted Seeded Glass Panels.
-31 Frosted Seeded White, -125 Frosted Seeded Amber

Material: Aluminum

Application: Outdoor

Approvals: UL/CUL Damp location listed.

Installation: Fits standard Outlet Box

Lamps: 1 GU24 Base lamp, at 26 watts max. (Not Included)

Electrical: 120V, 60 Hz, 6' wire

