

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## Specifications:

### Description:

The HSSQ4 is ideal for use in both new construction as well as remodel/retrofit. Light output is comparable to that of a typical 60W incandescent downlight, providing up to 75% energy savings. The HSSQ4 is equipped with both Edison base adaptor and quick link connector allowing easy installation in many standard incandescent round recessed housings.

### Construction:

- Diffused polycarbonate lens controls direct glare from the LEDs
- Easy installation with (3) friction spring clips
- Can be installed in most 4" round recessed housings
- Dimmable to 10% with many dimmers
- Lumen output and distribution comparable to a 60W incandescent lamp
- Suitable for use in IC or NON-IC Applications
- Provided with quick link for use with E26 Edison Base adapter

### Performance:

Input Power	9W
Input Voltage	120V
Input Frequency	60Hz
Lumens/LPW	630/70 (LM-79)
CCT	3000K
CRI	90
Life	50,000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Min. Start Temp	-30° C
Max. Operating Temp	30° C
Warranty	5 year warranty
Labels	cULus Wet location listed ENERGY STAR® qualified

## HSSQ4-WH-30K

### Images:



### Dimensions:

Width: 5.3"

Height: 3"