




# C6ICAT

## 6" IC Airtight Incandescent Housing



**Description:** The C6ICAT is a 6" IC, airtight, incandescent downlight housing, specifically designed to provide the contractor with the best value downlight.

**Application:** Ideal for tract and manufactured housing construction, the C6ICAT can also be used for most light commercial and residential applications where insulated ceilings require an IC rated downlight.

**Trim:** Trims use coil or torsion springs to attach to housing and provide a snug fit against the ceiling plane.

**Approvals:** UL/CUL Damp Location Listed. IC listed for direct contact with insulation. Air tight tested to ASTM E283 standards. Meets State of Washington and California Title 24 Restricted air flow requirements.

**Housing:** Small footprint, 22 gauge galvanized platform for rigid support. Snap-on J-box doors provide easy access for wiring and field inspection. Housing adjusts up to 1-1/2" to accommodate different ceiling thicknesses. Ceiling gasket is supplied with housing.

**Installation:** Pre-installed bar hangers with locking screws, integral nail, and alignment tab for wood joist construction. Hangers accommodate ceiling joists of up to 24 inches on-center. Captive bar hangers secure housing in place and can be reoriented 90° to housing.

**Lamps:** Housing socket plate adjusts vertically for various lamp sizes. For use with PAR30, PAR38, BR30, BR40 or A19 lamp. Lamp supplied by others.

**Electrical:** High temperature porcelain socket with plated brass or copper screw shell. Thermal protector prevents fixture from overheating when improperly installed or over-lamped.

### HOUSING

#### C6ICAT

### TRIMS



**610W**  
60W PAR30, 65W BR30  
White Half Baffle



**610B**  
60W PAR30, 65W BR30  
Black Half Baffle



**620W**  
75W PAR30/PAR38,  
65W BR30, 90W BR40  
White Full Baffle



**620B**  
75W PAR30/PAR38,  
65W BR30, 90W BR40  
Black Full Baffle



**614W**  
60W PAR38/BR40  
White Half Baffle



**614B**  
60W PAR38/BR40  
Black Half Baffle



**630C**  
60W PAR30, 65W BR30  
Clear Reflector



**630G**  
60W PAR30, 65W BR30  
Gold Reflector



**690W**  
60W PAR30, 65W BR30  
White Open Ring



**694W1**  
60W PAR38, 65W BR40  
White Open Ring



**602**  
40W A19  
Drop Lens\*



**601A**  
40W A19  
Flush Albalite Lens\*



**650W**  
75W PAR30, 65W BR30  
White Eyeball

\*Wet location.