



* Representative image

HW-J121005CHQRW

by Wiegmann
Catalog ID: HW-J121005CHQRW

NEMA 4X JIC Continuous Hinge Quick Release Padlockable With Window
12X10X5 Fiberglass-Opaque

Fiberglass construction is designed to protect electrical and electronic equipment in commercial or industrial environments from dust, dirt, oil, water and other corrosive materials. A wide variety of Non-Metallic enclosures are available.

- Constructed of molded fiberglass
- Windowed cover with continuous hinge and quick-release padlockable latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

Product Details

General

Color	Gray
Cover Type	Hinged Cover with Window
Material	Fiberglass
Mounting Type	Wall Mount
Series	JIC
Type	Enclosure
UPC	786725857432

Dimensions

Actual Depth	5.21 in
Actual Height	13.56 in
Actual Width	11.43 in
Cubic Capacity	600 cu.in
Depth	5 in
Height	12 in
Weight	6.5 lb
Width	10 in

Certifications and Compliance

Certified Listed	cULus
Nema Rating	4X

UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	1
-----------------	---