



* Representative image

Grounding Clamp

by ANDERSON
Catalog ID: K2S40

Grounding Clamp, Copper Split-Bolt, Threaded Stud, Two Cables

Product Details

General

| | |
|--|--------------|
| Bolt Installation Torque (Recommended) | 0 ft-lbs |
| Material | Bronze |
| Material - Hardware | Bronze |
| Number of Stud Threads | 11 |
| UPC | 096359318569 |

Dimensions

| | |
|-----------------|----------|
| Diameter - Stud | 0.625 in |
| Weight | 0.588 lb |

Conductor Related

| | |
|---|---------------|
| Conductor Diameter (Ground Tap) - Maximum | 0 in |
| Conductor Diameter (Ground Tap) - Minimum | 0 in |
| Conductor Diameter - Maximum | 0.522 in |
| Conductor Diameter - Minimum | 0.325 in |
| Conductor Diameter Range | 0.325 - 0.522 |
| Conductor Type | Copper |
| Messenger Diameter - Maximum | 0 in |
| Messenger Diameter - Minimum | 0 in |

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com