

Connector, Parallel Groove

by ANDERSON
Catalog ID: K2

Two bolt Bronze Parallel Groove Connector

- Has no cable separator.



* Representative image

Product Details

General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	0 ft-lbs
Cover Available	No
Inhibitor Loaded	No
Item Type	4D
Material	Bronze
Material - Body	Bronze Alloy
Material - Body Halves	Bronze Alloy
Material - Bolt	Silicon Bronze
Material - Bottom Member	Bronze Alloy
Material - Hardware	Silicon Bronze
Material - Spacer	Bronze Alloy
Plated	N
Plating	No
Plating Type	Unplated
Product Category	Mechanical Connectors
Style	Two Bolt
Trade Name	NO
UPC	096359318514
UPC 12 Digit	781810288344

Dimensions

Bolt Diameter	0.380 in
Diameter - Bolt	0.38 in

Dimension - Hole Size mm	0 mm
Weight	0.294 lb

Conductor Related

Conductor Diameter (Tap) - Maximum	0.419 in
Conductor Diameter (Tap) - Minimum	0.128 in
Conductor Diameter - Maximum	0.419 in
Conductor Diameter - Minimum	0.26 in
Conductor Diameter Range	0.26 - 0.419

Certifications and Compliance

Certification - CSA Approved	N
Certification - ETL	N
Certification - UL Recognized	N
Certification - cULus	N
Standards - RoHS Compliance Status	UI
UL Listed	No

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
 210 N. Allen Centralia, MO 65240 USA
 Phone: (573) 682-5521
 Fax: (573) 682-8475
 Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
 Fax: +1-573-682-8516
 Email: hpsintlcs@hubbell.com