



Versamate Series 100A 3 Pole 4 Wire Receptacle Assembly - AT Type

By Killark
Catalog # [VR1034](#)

100A 3 Pole 4 Wire Receptacle Assembly - AT Type

Features

- Patented “Breech-Lock” cap serves as both flip lid and screw cover.
- Patented notch in cap arm holds cap open for easy plug insertion or maintenance.
- Type 4X rating when inserted into VersaMate receptacle and locking ring is tightened.
- Patented pin design uses slotted spring clip which avoids excessive wear while providing continuous electrical pin to sleeve contact.
- “Increased Safety” type box terminals with gripper ribs securely clamp around conductors.
- Boxes come with a green grounding screw.

Application

Suitable for indoor or outdoor use. Applications include the wet, cold, hosedown, hazardous or corrosive areas in such industrial applications as:Pulp & Paper Mills, Electrical Power Plants, Petrochemical Plants, Wastewater Treatment, Marine, Docks, Ports, Construction Sites, Breweries, Refineries, Chemical Plants, Grain Facilities , Textile Manufacturing, Food Processing Facilities


Specifications

EU RoHS Indicator Contact Manufacturer

Conductor

Number Of Wires 3

Current



Frequency Rating	50-400 Hz
Amperage Rating	100 A
Voltage Rating	• 600 VAC • 250 VDC

Dimensions

Weight	3.48 lb.
Height	4.75 in
Width	4.25 in
Length	5.37 in
Dimensions	5.37 in x 4.25 in x 4.75 in

General

Style	Style I
UPC	783936078656
Type	Pin & Sleeve
Material	• Body-Copper-free aluminum • Contacts-Brass • Spring tensioner-Patented beryllium copper • External screws-316 stainless steel
Finish Type	Baked Powder Epoxy/Polyester Finish
Series	VersaMate Series

Product Assets

[Installation Manual \[English\]](#)