



Versamate Series 30A 4 Pole 4 Wire Receptacle Assembly - AT Type

By Killark
Catalog # [VR3044](#)

30A 4 Pole 4 Wire Receptacle Assembly - AT Type

Features

- Patented “Breech-Lock” cap serves as both flip lid and screw cover.
- Patented notch in cap arm holds cap open for easy plug insertion or maintenance.
- Type 4X rating when inserted into VersaMate receptacle and locking ring is tightened.
- Patented pin design uses slotted spring clip which avoids excessive wear while providing continuous electrical pin to sleeve contact.
- “Increased Safety” type box terminals with gripper ribs securely clamp around conductors.
- Boxes come with a green grounding screw.

Application

Suitable for indoor or outdoor use. Applications include the wet, cold, hosedown, hazardous or corrosive areas in such industrial applications as:Pulp & Paper Mills, Electrical Power Plants, Petrochemical Plants, Wastewater Treatment, Marine, Docks, Ports, Construction Sites, Breweries, Refineries, Chemical Plants, Grain Facilities , Textile Manufacturing, Food Processing Facilities


Specifications

EU RoHS Indicator Contact Manufacturer

Conductor

Number Of Wires 4

Current



Frequency Rating 50-400 Hz
Amperage Rating 30 A
Voltage Rating • 600 VAC
 • 250 VDC

Dimensions

Weight 1.46 lb.
Height 3.89 in
Width 3.41 in
Length 3.25 in
Dimensions 3.25 in x 3.41 in x 3.89 in

General

Style Style I
UPC 783936078786
Type Pin & Sleeve
Material • Body-Copper-free aluminum
 • Contacts-Brass
 • Spring tensioner-Patented beryllium copper
 • External screws-316 stainless steel

Finish Type Baked Powder Epoxy/Polyester
Series VersaMate Series

Product Assets

[Installation Manual \[English\]](#)