



COMPONENT PARTS/ACCESSORIES/OPTIONS • HID FIXTURES

Mounting Boxes



Pendant



Ceiling



EAC^①



Wall Bracket



25° Stanchion



HIC-BEIGE replacement wiring plug for EZBx Wall Bracket



Ezcup
Close up plug for EZ mounting boxes. Used for maintenance when fixture is removed for service.



Replacement Globe & Support Assemblies

REPLACEMENT GLOBE & GLOBE SUPPORT ASSEMBLY

SERIES	LAMP TYPE	WATTAGE	CATALOG NUMBER
EZS	HPS	50-150	EZGS1
EZH	MH	70-250	
EZP	MHP	150, 175, 250	
EZS	HPS	250, 400	EZGS2
EZH	MH	400	
EZP	MHP	320-400	

MOUNTING BOXES				
HUB SIZE	CATALOG NUMBER			
	PENDANT	CEILING	BRACKET	STANCHION
3/4"	EZA2	EZX2**	EZB2	—
1"	EZA3	EZX3	EZB3	—
1-1/4" / 1-1/2"	—	—	—	EZD4*

* Supplied as 1-1/2" NPT with 1-1/2" x 1-1/4" reducer
 ** 25 cu. in. below EZTB tangs.

EZ OPTIONS

Instant Restart Option

Factory installed special ignitor provides hot lamp instant restart of HPS lamps after power interruption of up to 1 minute. Available for 50, 70, 100 and 150 watt HPS lamps only. Add suffix "R" to fixture catalog number (50/60 Hz).


Quartz Emergency Lamp

Factory installed special auxiliary quartz relay and D.C. bayonet base socket installed to accept 100 watt, 120 volt quartz (100Q/DC) lamps only. Lamps not supplied. Refer to Hazardous Location Application Data chart to verify suitability. Add suffix "Q" to fixture catalog number.

Ballast Protection Cutout

Optional factory installed special ballast protector replaces the standard HPS ignitor and applies starting pulse to the lamp for 10 to 15 seconds each time voltage is supplied to the ballast. If the lamp has not ignited by the end of the time period, the starter will cease pulsing. Used to eliminate the continuous high voltage pulsing of the ignitor when end of life, lamp cycling, or missing lamp conditions exist. Available for 70, 100, 150, 250 and 400 watt HPS fixtures. Add suffix "BP" to fixture catalog number.

Notes: BP & R cannot be used together.
 Q & R cannot be used together.



FACTORY SEALED
 Class I, DIV. 1 BCD
 Class II, DIV. 1&2 EFG
 CLASS III
 NEMA 3, 4X IP66
 *40°C ambient T3 Rated

PHOTO CELL FIELD KITS WITH HKB - GL BOX AND COVER

VMHKPC1	120VAC
VMHKPC2	208-277VAC
VMHKPC3	347VAC



LIGHTING

COMPONENT PARTS/ACCESSORIES




EZG1



VMAG40S

GUARDS				
CATALOG NUMBER	SERIES	LAMP TYPE	WATTAGE	DESCRIPTION
EZG1	EZS	HPS	50-150	Painted cast aluminum
	EZH	MH	70-250	
	EZP	MHP	150, 175, 250	
VMAG40S	EZH	MH	400	Cadmium plated steel
	EZP	MHP	320-400	



[Ⓢ] For VMAG40S with bottom closure order part number VMAG40SBC.



VMPD40



EZTB



VMPA40



HRD400
HRD400ALZ (pictured)



EZCB



EZMO

REFLECTORS	
CATALOG NUMBER	DESCRIPTION
VMPD40	Standard dome. fiberglass reinforced polyester
VMPA40	30° Angle fiberglass reinforced polyester
HRD400	Deep dome. Aluminum with white finish [Ⓢ]
HRD400ALZ	Deep dome with specular anodized finish [Ⓢ]

REPLACEMENT CONNECTION BLOCKS AND LAMP SOCKET	
CATALOG NUMBER	DESCRIPTION
EZTB	Female (goes in splice box)
EZCB	Male (goes in top of fixture body)
EZMO	Replacement lamp socket with gasket

[Ⓢ] For clearance, wall mount models require standoff of 1/2" if not bottom feed; 1-1/2" if bottom feed.