

Connector, Parallel Groove

by ANDERSON
Catalog ID: KR1

Two bolt Bronze Parallel Groove Connector

- Has conductor separator.



* Representative image

Product Details

General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	0 ft-lbs
Cover Available	No
Inhibitor Loaded	No
Material	Bronze
Material - Body	Bronze Alloy
Material - Body Halves	Bronze Alloy
Material - Bolt	Silicon Bronze
Material - Bottom Member	Bronze Alloy
Material - Hardware	Silicon Bronze
Material - Spacer	Bronze Alloy
Plating	No
Product Category	Mechanical Connectors
Style	Two Bolt
UPC	096359318729

Dimensions

Bolt Diameter	0.310 in
Diameter - Bolt	0.31 in
Weight	0.196 lb

Conductor Related

Conductor Diameter (Tap) - Maximum	0.373 in
Conductor Diameter (Tap) - Minimum	0.128 in
Conductor Diameter - Maximum	0.373 in

Conductor Diameter - Minimum	0.232 in
Conductor Diameter Range	0.232 - 0.373

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	7200 EA
-----------------	---------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com