

Connector, Parallel Groove

by ANDERSON
Catalog ID: KR2

Two bolt Bronze Parallel Groove Connector

- Has no cable separator.



* Representative image

Product Details

General

| | |
|--|-----------------------|
| Bolt Head Type | Hex |
| Bolt Installation Torque (Recommended) | 0 ft-lbs |
| Cover Available | No |
| Inhibitor Loaded | No |
| Material | Bronze |
| Material - Body | Bronze Alloy |
| Material - Body Halves | Bronze Alloy |
| Material - Bolt | Silicon Bronze |
| Material - Bottom Member | Bronze Alloy |
| Material - Hardware | Silicon Bronze |
| Material - Spacer | Bronze Alloy |
| Plating | No |
| Product Category | Mechanical Connectors |
| Style | Two Bolt |
| UPC | 096359318743 |

Dimensions

| | |
|-----------------|----------|
| Bolt Diameter | 0.380 in |
| Diameter - Bolt | 0.38 in |
| Weight | 0.392 lb |

Conductor Related

| | |
|------------------------------------|----------|
| Conductor Diameter (Tap) - Maximum | 0.419 in |
| Conductor Diameter (Tap) - Minimum | 0.162 in |

| | |
|------------------------------|--------------|
| Conductor Diameter - Maximum | 0.419 in |
| Conductor Diameter - Minimum | 0.26 in |
| Conductor Diameter Range | 0.26 - 0.419 |

Certifications and Compliance

| | |
|-----------|----|
| UL Listed | No |
|-----------|----|

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com